



### Main

Range	Unica
Device application	Signalling
Product or component type	Buzzer
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Ivory (RAL 9010)

### Complementary

Current consumption	40 mA
Type of setting	Volume can be adjusted using a screw
Operating time	0...60 ms
Connections - terminals	Screw terminals
Acoustic level	Between 76 and 80 dB
Cable cross section	0.75...1.5 mm <sup>2</sup> flexible cable 0.75...1.5 mm <sup>2</sup> rigid cable
Material	ASA + PC: mechanism cover
Standards	LV directive EMC directive CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 mm
Depth	42 mm
Width	45 mm
Height	45 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net weight	0.0475 kg
------------	-----------

## Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Oil Petrol Acetone Alcohol Bleach Window-cleaning fluid Liquid soap UV resistant

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	50 g
Package 1 Height	4.4 cm
Package 1 width	6.7 cm
Package 1 Length	6.8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	500 g
Package 2 Height	12 cm
Package 2 width	12.5 cm
Package 2 Length	17.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Weight	2 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------