

Product datasheet

Specifications



Unica Top/Class - electronic bell - 230V AC - 2 m - clip-in - aluminium

MGU3.786.30

Main

Range	Unica
Device application	Signalling
Product or component type	Electronic bell
Aesthetic name	Unica Top - Unica Class
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Aluminium

Complementary

Current consumption	14 mA
Type of setting	5 programmable melodies
Connections - terminals	Screw terminals
Acoustic level	70 dB/1m
Cable cross section	0.75...1.5 mm ² flexible cable 0.75...1.5 mm ² rigid cable
Connected auxiliaries	3 indicator lights connected in parallel 10 standard push-buttons connected in parallel
Material	ASA + PC: mechanism cover
Standards	IEC 62080
Product certifications	CE
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	33 mm
Depth	44 mm
Width	45 mm
Height	45 mm
Net weight	0.11 kg

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Liquid soap Alcohol Acetone Window-cleaning fluid UV resistant Petrol Bleach Oil

Packing Units

Package 1 Weight	0.146 kg
Package 1 Height	0.650 dm
Package 1 width	0.750 dm
Package 1 Length	0.850 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------