

Product datasheet

Specifications



Unica Allegro - cover frame - 1 module - white

MGU4.101.18

Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Allegro
Number of modules	1 module
Fixing mode	Clip-in
Cover frame colour tint	White

Complementary

Material	ASA + PC: cover frame
Standards	EN 60669-1
Height	80 mm
Width	116 mm
Depth	14 mm
Net weight	0.017 kg
Market segment	Residential Small commercial

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Acetone Alcohol Window-cleaning fluid Liquid soap Oil UV resistant Bleach Petrol

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	23.0 g

Package 1 Height	1 cm
Package 1 width	11.6 cm
Package 1 Length	8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	595.0 g
Package 2 Height	12.2 cm
Package 2 width	17.5 cm
Package 2 Length	26 cm
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Weight	30.9 kg
Package 3 Height	77 cm
Package 3 width	80 cm
Package 3 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------