

# Product datasheet

Specifications



## Unica Allegro - cover frame - 2 modules - ivory

MGU4.102.25

### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Allegro
Number of modules	2 modules
Fixing mode	Clip-in
Cover frame colour tint	Ivory

### Complementary

Material	ASA + PC: cover frame
Standards	EN 60669-1
Height	80 mm
Width	116 mm
Depth	14 mm
Net weight	0.018 kg
Market segment	Small commercial Residential

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Alcohol Petrol Liquid soap Acetone UV resistant Oil Bleach Window-cleaning fluid

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	20.0 g

Package 1 Height	1 cm
Package 1 width	11.5 cm
Package 1 Length	8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	548.0 g
Package 2 Height	12.2 cm
Package 2 width	17.5 cm
Package 2 Length	26 cm
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Weight	29.996 kg
Package 3 Height	77 cm
Package 3 width	80 cm
Package 3 Length	60 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------