

Product datasheet

Specifications



Unica Allegro - cover frame - 4 modules - white



MGU4.104.18

Main

| | |
|---------------------------|---------------|
| Range | Unica |
| Device application | Mounting |
| Product or component type | Cover frame |
| Aesthetic name | Unica Allegro |
| Number of modules | 4 modules |
| Fixing mode | Clip-in |
| Cover frame colour tint | White |

Complementary

| | |
|----------------|---------------------------------|
| Material | ASA + PC: cover frame |
| Standards | EN 60669-1 |
| Height | 80 mm |
| Width | 139 mm |
| Depth | 14 mm |
| Net weight | 0.02 kg |
| Market segment | Small commercial Residential |

Environment

| | |
|------------------------------|---|
| IK degree of protection | IK01 |
| IP degree of protection | IP20 |
| Environmental characteristic | Oil Petrol Window-cleaning fluid Alcohol Liquid soap Acetone Bleach UV resistant |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 26.0 g |

| | |
|------------------------------|----------|
| Package 1 Height | 1.4 cm |
| Package 1 width | 8 cm |
| Package 1 Length | 14 cm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Weight | 172.5 g |
| Package 2 Height | 7.5 cm |
| Package 2 width | 9.5 cm |
| Package 2 Length | 25 cm |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 600 |
| Package 3 Weight | 30.52 kg |
| Package 3 Height | 75 cm |
| Package 3 width | 80 cm |
| Package 3 Length | 60 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|