

# Product datasheet

Specifications



## Unica Plus - cover frame - 3 modules - manganese blue/white

MGU6.103.873

### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Plus
Number of modules	3 modules
Fixing mode	Clip-in
Cover frame colour tint	Manganese blue
Decoration colour	White

### Complementary

Material	ASA + PC: intermediate part ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	116 mm
Width	80 mm
Depth	13.7 mm
Net weight	0.021 kg

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Alcohol UV resistant Petrol Bleach Oil Window-cleaning fluid Acetone Liquid soap

### Packing Units

Package 1 Weight	24.200 g
Package 1 Height	7.000 mm
Package 1 width	9.000 mm

---

Package 1 Length	31.000 mm
------------------	-----------

---

## Offer Sustainability

---

Sustainable offer status	Green Premium product
--------------------------	-----------------------

---

---

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

---

---

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

---

---

Mercury free	Yes
--------------	-----

---

---

RoHS exemption information	Yes
----------------------------	-----

---

---

China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
-----------------------	---

---

---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---