

Product datasheet

Specifications



Unica Plus - cover frame - 3 modules - mink/white

MGU6.103.874

Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Plus
Number of modules	3 modules
Fixing mode	Clip-in
Cover frame colour tint	Mink
Decoration colour	White

Complementary

Material	ASA + PC: intermediate part ABS (acrylonitrile butadiene-styrene): cover frame
Standards	EN 60669-1
Height	116 mm
Width	80 mm
Depth	13.7 mm
Net weight	0.021 kg
Market segment	Small commercial Residential

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Bleach Alcohol Window-cleaning fluid Oil UV resistant Petrol Liquid soap Acetone

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	26 g
Package 1 Height	1 cm
Package 1 width	11.6 cm
Package 1 Length	8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	331 g
Package 2 Height	7.4 cm
Package 2 width	9.4 cm
Package 2 Length	32 cm
Unit Type of Package 3	S02
Number of Units in Package 3	30
Package 3 Weight	1.305 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------