

# Product datasheet

Specifications



## Unica Top - cover frame - 3 modules - opal titanium/aluminium

MGU66.103.095

### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of modules	3 modules
Fixing mode	Clip-in
Cover frame colour tint	Opal titanium
Decoration colour	Aluminium

### Complementary

Material	ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	116 mm
Width	80 mm
Depth	13.7 mm
Net weight	0.072 kg

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Alcohol Acetone Window-cleaning fluid UV resistant Oil Bleach Liquid soap Petrol

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	72 g

Package 1 Height	1.5 cm
Package 1 width	8.1 cm
Package 1 Length	11.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Weight	272 g
Package 2 Height	12 cm
Package 2 width	7 cm
Package 2 Length	19 cm
Unit Type of Package 3	S02
Number of Units in Package 3	24
Package 3 Weight	2.493 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------