

# Product datasheet

Specifications



## Unica Top - cover frame - 3 modules - onyx copper/aluminium

MGU66.103.096

### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of modules	3 modules
Fixing mode	Clip-in
Cover frame colour tint	Onyx copper
Decoration colour	Aluminium

### Complementary

Material	ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	116 mm
Width	80 mm
Depth	13.7 mm
Net weight	0.072 kg
Market segment	Residential Small commercial

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Liquid soap UV resistant Window-cleaning fluid Oil Acetone Petrol Bleach Alcohol

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	72 g
Package 1 Height	1 cm
Package 1 width	11.6 cm
Package 1 Length	8 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Weight	275 g
Package 2 Height	6.5 cm
Package 2 width	12.4 cm
Package 2 Length	18.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	24
Package 3 Weight	3 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------