

Product datasheet

Specifications



Unica Top - cover frame - 3 modules - cherry tree/graphite

MGU66.103.2M2

Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Top
Number of modules	3 modules
Fixing mode	Clip-in
Cover frame colour tint	Cherry tree
Decoration colour	Graphite

Complementary

Material	ASA + PC: intermediate part Zamak: cover frame
Standards	EN 60669-1
Height	118 mm
Width	80 mm
Depth	13.7 mm
Net weight	0.745 kg
Market segment	Small commercial Residential

Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Oil Bleach Petrol UV resistant Window-cleaning fluid Liquid soap Alcohol Acetone

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	35 g
Package 1 Height	1.7 cm
Package 1 width	9.5 cm
Package 1 Length	12.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Weight	174 g
Package 2 Height	7 cm
Package 2 width	13 cm
Package 2 Length	19 cm
Unit Type of Package 3	S02
Number of Units in Package 3	24
Package 3 Weight	1.847 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------