

# Product datasheet

Specifications



## KNX universal dimming actuator LL REG-K/4x230/250W

MTN6710-0004

### Main

Range Of Product	KNX
Product Or Component Type	Dimming actuator
Operating Mode	Manual KNX bus system
Bus Type	KNX

### Complementary

Total Number Of 18 Mm Modules	8
Mounting Support	DIN rail
[Ue] Rated Operational Voltage	220...230 V 110...130 V
Network Frequency	50/60 Hz
Number Of Outputs	4
Local Signalling	LED
Load Type	Incandescent lamps: 4...250 W at 230 V AC Halogen lamps: 4...250 W at 230 V AC LV halogen lamps: 25...250 VA at 12 V AC (wound transformer) LV halogen lamps: 4...250 W at 12 V AC (electronic transformer) Compact fluorescent lamp: 4...125 W at 230 V AC (RC mode) Energy saving lamp: 4...125 W at 230 V AC (RC mode) LED lamp: 4...125 W at 230 V AC (RC mode) Compact fluorescent lamp: 25...45 W at 230 V AC (RL LED mode) Energy saving lamp: 25...45 W at 230 V AC (RL LED mode) LED lamp: 25...45 W at 230 V AC (RL LED mode) Incandescent lamps: 4...125 W at 110 V AC Halogen lamps: 4...125 W at 110 V AC LV halogen lamps: 25...125 VA at 12 V AC (wound transformer) LV halogen lamps: 4...125 W at 12 V AC (electronic transformer) Compact fluorescent lamp: 4...60 W at 110 V AC (RC mode) Energy saving lamp: 4...60 W at 110 V AC (RC mode) LED lamp: 4...60 W at 110 V AC (RC mode) Compact fluorescent lamp: 12...22 W at 110 V AC (RL LED mode) Energy saving lamp: 12...22 W at 110 V AC (RL LED mode) LED lamp: 12...22 W at 110 V AC (RL LED mode)

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Package 1 Width</b>	12.300 cm
<b>Package 1 Length</b>	27.700 cm
<b>Package 1 Weight</b>	576.000 g
<b>Unit Type Of Package 2</b>	S03
<b>Number Of Units In Package 2</b>	6
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	30.000 cm
<b>Package 2 Length</b>	40.000 cm
<b>Package 2 Weight</b>	3.946 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)