# **Product datasheet**

Specification





Wall mounted polyester enclosure, Thalassa PLM, glazed door, 1056x852x350mm, IP66, IK08, RAL 7035

NSYPLM108TG

#### Main

| Range              | Thalassa  |
|--------------------|---|
| Product Name       | Thalassa PLM                                      |
| Device Short Name  | PLM   |
| Enclosure Type     | Multi-purpose                                     |
| Category           | Compact enclosure                                 |
| Nominal Height     | 1056 mm   |
| Nominal Width      | 852 mm  |
| Nominal Depth      | 350 mm  |
| Enclosure Mounting | Wall mounted                                      |
| Device Composition | 1 body<br>1 door<br>1 lock                        |
| Door Type          | Transparent                                       |
| Lock Type          | 4 points lock, handle with 5 mm double bar insert |

# Complementary

| Number Of Locks             | 1  |
|-----------------------------|--|
| Mounting Plate Description  | Without mounting plate   |
| Accessibility For Operation | Front  |
| Removable Parts             | Door by hinges   |
| Material                    | Body: polyester reinforced with fibreglass<br>Door: tempered glass |
| Colour                      | Grey (RAL 7035)  |
| Standards                   | IEC 62208 NEMA classification 4X NEMA classification 13            |
| Product Certifications      | UL   |
| Electrical Insulation Class | Class II   |

#### **Environment**

| Ip Degree Of Protection                  | IP66 conforming to IEC 60529   |
|--|--------------------------------|
| Ik Degree Of Protection                  | IK08 conforming to IEC 62262   |
| Fire Resistance                          | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For<br>Operation | -4080 °C                       |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 88 cm     |
| Package 1 Width              | 38 cm     |
| Package 1 Length             | 109 cm    |
| Package 1 Weight             | 35.494 kg |
| Unit Type Of Package 2       | PAM       |
| Number Of Units In Package 2 | 4         |
| Package 2 Height             | 120 cm    |
| Package 2 Width              | 100 cm    |
| Package 2 Length             | 165 cm    |
| Package 2 Weight             | 145 kg    |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |