# **Product datasheet**

Specifications





Wall mounted polyester enclosure, Thalassa PLM, plain door, 308x255x160mm, IP66, IK10, RAL 7035

NSYPLM3025G

#### Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	308 mm
Nominal Width	255 mm
Nominal Depth	160 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body
	1 door
	1 lock
Door Type	Plain
Lock Type	3 mm double-bar lock

### Complementary

Number Of Locks	1
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208 NEMA classification 13 NEMA classification 4X
Product Certifications	UL
Electrical Insulation Class	Class II

### Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Operation	-4080 °C

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.500 cm
Package 1 Width	26.500 cm
Package 1 Length	32.500 cm
Package 1 Weight	3.414 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	90
Package 2 Height	150.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	349.510 kg

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations