# **Product datasheet**

Specifications





# Floor-Standing Cabling Rack 24U W800D1000 Fixed 19" Glazed Door R7035

NSYVDA24U810E

- ! Discontinued on: Aug 20, 2023
- ! End-of-service on: Jan 27, 2024

#### ! Discontinued

#### Main

Range	Actassi
Product Name	Actassi VDA
Product Or Component Type	19" enclosure
Device Application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure Type	Network Cabinet
Support Equipment	4 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front Face	Glazed door
Door Type	Front glazed door - with 2 points locking system (key: 333) - reversible opening at 180 °  Rear plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility For Operation	Side Top Front Rear
Removable Parts	Front door removable toolless Top blanking plate Bottom blanking plate Side panels removable toolless Rear door removable toolless
Colour	Door: light grey (RAL 7035) Panels: light grey (RAL 7035) Top and bottom: light grey (RAL 7035) Structure: dark grey (RAL 7011)

## **Complementary**

Device Composition	1 x glazed door front			
	2 x panels side			
	1 x assembled structure CBLX torx			
	1 x roof with removable blanking plate top 4 x levelling feets 1 x plain door rear 4 x 19" uprights			
			1 x fixing kit (screws, cage nuts)	
				10 x earthing connections
			Load Rating	400 kg static
	250 kg dynamic			
Back Face	Plain door			
Side Face	Panel			

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Cut-Out	1 cut-outbottom
	1 cut-outtop side panel
	1 cut-outtop - split in 3 parts
Installation Mode	Floor-standing
Material	Sheet steel: structure
	Sheet steel: door
	Sekurit glass: door
	Galvanized steel: upright
	Sheet steel: panel
Surface Finish	Epoxy-polyester powder
Width	800 mm
Height	1200 mm
Depth	1000 mm
Net Weight	91 kg
Number Of Rack Unit	24U
Targeted Region	Europe

## **Environment**

Ik Degree Of Protection	IK08 conforming to IEC 62262
Ip Degree Of Protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	84.0 cm
Package 1 Width	103.0 cm
Package 1 Length	113.0 cm
Package 1 Weight	91.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations