



ⓘ Discontinued

Commercial status

Discontinued on: 23 January 2021

End-of-service on: 23 January 2021

NSYVDAC42U86 has not been replaced. Please contact your customer care centre for more information.

Main

Range	Actassi
Product name	Actassi VDA
Product or component type	19" enclosure
Device application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure type	Network Cabinet
Support equipment	2 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front face	Glazed door
Door type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 ° Rear partial plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility for operation	Top Rear Side Front
Removable parts	Front door removable toolless Top blanking plate Bottom blanking plate Rear partial door removable toolless Rear partial panel removable toolless
Colour	Door: light grey (RAL 7035) Panels: light grey (RAL 7035) Top and bottom: light grey (RAL 7035) Structure: dark grey (RAL 7011)

Complementary

Device composition	1 x glazed door front 2 x 19" uprights front 1 x assembled structure CBLX torx 1 x roof with removable blanking plate top 4 x levelling feet 1 x partial panel (6U) rear
--------------------	---

	1 x partial plain door rear
Load rating	400 kg static 250 kg dynamic
Back face	Partial plain door
Side face	Panel
Number of cut-out	1 cut-outbottom 1 cut-outtop side panel 1 cut-outtop - split in 3 parts
Installation mode	Floor-standing
Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright Sheet steel: panel
Surface finish	Epoxy-polyester powder
Width	800 mm
Height	2000 mm
Depth	600 mm
Net weight	80 kg
Number of rack unit	42U
Targeted region	Europe

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	80 kg
Package 1 Height	213 cm
Package 1 width	84 cm
Package 1 Length	64 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------