Product datasheet

Specifications





Wander plug, Mureva PK, Fast connection, 16A, 3P+E, 400V, IP67

PKX16M734

Main

Range	Mureva
Product Or Component Type	Wander plug
Device Short Name	Mureva plug
Plug, Socket Category	Low voltage
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Plug, Socket, Control Station Shape	Straight
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	380415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Fast connection
Cable Cross Section	12.5 mm²
Cable Outer Diameter	815 mm
Cable Entry	Fair lead Cable gland
Thread Type	Pg 16
Net Weight	0.201 kg
Height	139 mm
Width	81 mm
Depth	81 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Ot I I -	150 00000 /	
Standards	IEC 60309-1	
	150 00000 0	
	IEC 60309-2	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP67 conforming to IEC 60529	
Ik Degree Of Protection	IK08 conforming to EN 62262	
Fire Resistance	850 °C conforming to IEC 60695-2-11	
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C	
Operating Altitude	2000 m	
Ambient Air Temperature For Operation	35 °C (86400 s) -2540 °C	

Packing Units

PCE
1
7.8 cm
7.8 cm
15.2 cm
184.0 g
BB1
10
18.0 cm
26.6 cm
27.0 cm
2.046 kg
S03
20
30.0 cm
30.0 cm
40.0 cm
4.579 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations