

# Product datasheet

Specifications



## Pragma interface - for surface enclosure - 2 x 13 or 18 modules - without door

PRA06218

Discontinued on: Nov 20, 2023

Discontinued

### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Interface
Width	200 mm outside:
Height	450 mm
Depth	115 mm
Nb Of 18 Mm Modules Per Row	13
	18
Nb Of Horizontal Rows	2
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 x identification label 1 x plain plate per row 1 x front face and back connection
Type Of Door	Without

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	26
	36
Total Number Of 18 Mm Modules	14
Number Of Plates	3 for plain plate
[In] Rated Current	63 A
	90 A
[Ui] Rated Insulation Voltage	400 V
Type Of Rail	Without
Mounting Plate Description	Without mounting plate
Cable Entry	Cable or tube
	Trunking
	Removable plates
	Cut-out plates
Enclosure Material	Back part: technoplastic
	Front face: technoplastic
Colour	Enclosure: white (RAL 9016)
	Front face: grey (RAL 7004)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Market Segment	Residential Small commercial
Embedding Depth	0 mm
Internal Depth	95 mm

## Environment

Fire Resistance	Back part: 750 °C Front face: 750 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.500 cm
Package 1 Width	22.000 cm
Package 1 Length	46.000 cm
Package 1 Weight	1.700 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	57
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	108.900 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations