

Product datasheet

Specifications



Actassi FL-C Fibre Optic Adapter LC Duplex SM rectangle x1

VDIB6052003

Main

Range	Actassi
Product or component type	Singlemode fibre optic adapter
Provided equipment	Without screws
Colour	Blue
Type of packing	Bag
Quantity per set	1

Complementary

Minimum number of matings	200 cycles
Optic fiber diameter	9/125 µm
Fibre performance	OS1 OS2
Connector type	LC duplex rect
Material	Zirconia: ferrule
Fixing mode	By clips Screws
Width	22 mm
Height	9.3 mm
Length	25 mm
Targeted region	Europe

Environment

Ambient air temperature for operation	-25...85 °C
Ambient air temperature for storage	-25...85 °C
Standards	LC adapter: TIA/EIA-604-10 A LC adapter: IEC 61754-20 Ed.2 ISO/IEC 11801:2011 Ed.2.2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	2.0 cm
Package 1 Width	13.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	5.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	150
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.082 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)