



Main

Range	Prisma
Range of product	Prisma G
Product or component type	Door
Range compatibility	Prisma G enclosure
Provided equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Type of door	Transparent
IP degree of protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

Complementary

Installation description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door opening side	Reversible
Number of locks	2
Door opening angle	130 °
Number of vertical modules [50 mm]	24
Enclosure material	Handle: polyamide Glass Cover frame: treated sheet steel
Quantity per set	Set of 1
Height	1230 mm
Width	600 mm
Depth	36 mm

Net weight	8.2 kg
Material	Glass
Surface finish	Smooth Matt
Colour	White (RAL 9001)

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	9.05 kg
Package 1 Height	5.5 cm
Package 1 width	62.5 cm
Package 1 Length	127 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Weight	123 kg
Package 2 Height	99 cm
Package 2 width	80 cm
Package 2 Length	127 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile