



Main

Range	Prisma
Product or component type	Door
Range compatibility	Prisma G enclosure
Provided equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Type of door	Plain
IP degree of protection	IP55

Complementary

Installation description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door opening side	Reversible
Number of locks	3
Door opening angle	180 °
Number of vertical modules [50 mm]	27
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	1450 mm
Width	600 mm
Depth	26 mm
Net weight	22.7 kg
Surface finish	Matt Smooth
Colour	White (RAL 9001)

Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22.701 kg
Package 1 Height	7.5 cm
Package 1 width	60 cm
Package 1 Length	145 cm
Unit Type of Package 2	P2M
Number of Units in Package 2	20
Package 2 Weight	454.02 kg
Package 2 Height	80 cm
Package 2 width	200 cm
Package 2 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile