



Main

Range	Prisma
Product or component type	Roof
Range compatibility	Prisma P enclosure
Installation description	Cubicle - width 800 mm, depth 600 mm Cubicle - width 650 + 150 mm
Provided equipment	Quarter-turn fasteners
Type of front cover	Plain

Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Smooth
Colour	White (RAL 9001)
Special colour options	Yes
Width	800 mm
Depth	600 mm
Net weight	5.02 kg
Quantity per set	Set of 1

Environment

IP degree of protection	IP55
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.9 kg
Package 1 Height	4 cm

Package 1 width	61 cm
Package 1 Length	81 cm
Unit Type of Package 2	P12
Number of Units in Package 2	40
Package 2 Weight	200.8 kg
Package 2 Height	80 cm
Package 2 width	80 cm
Package 2 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Halogen content performance	Halogen free product