



### Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for power outlet
Accessories included with enclosure	2 wiring straps 1 plate for push-button controls 4 plates for 65 x 85 power outlets
Mounting plate description	Without mounting plate

### Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	8
Total number of 18 mm modules	8
Number of horizontal rows	1
Electrical insulation class	Double insulation Class II
Number of openings of interface	4
Number of plates	1 for push-button controls 4 for 65 x 85 power outlets
Provided equipment	2 wiring strap 1 plate for push-button control 4 plate for 65 x 85 power outlet
Type of front cover	Transparent
Power dissipation in W	15 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	7
Number of terminal blocks	1 with 8 outgoers
Distribution block outgoers	4 x 10 mm <sup>2</sup>

	4 x 16 mm <sup>2</sup>
Locking options description	Optional keylock
Enclosure material	Housing: self-extinguishing polymer
Net weight	2 kg
Base dimension	90 x 100 mm
Width	236 mm
Height	460 mm
Depth	160 mm
Internal depth	91 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

## Environment

Standards	EN 62262 IEC 60439-3 EN 50262 IEC 60695-2-1 IEC 60529 IEC 670
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...40 °C

## Packing Units

Package 1 Weight	2.021 kg
Package 1 Height	4.700 dm
Package 1 width	2.560 dm
Package 1 Length	1.680 dm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------