

Product datasheet

Specifications



trip unit MA100 for Compact NS
100/160/250 circuit breakers,
magnetic, rating, 100A, 3 poles 3d

29120

⚠ Discontinued on: 30 Sept 2020

⚠ Discontinued

Main

Range	ComPact
Range Of Product	NS100...250
Product Or Component Type	Trip unit
Trip Unit Name	MA
Trip Unit Technology	Magnetic
Range Compatibility	ComPact NS100
Device Application	Motor
Number Of Poles	3P
Protected Poles Description	3t
Trip Unit Protection Functions	I
Protection Type	I : for short-circuit protection (magnetic)
Trip Unit Rated Current	100 A at 65 °C
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable
[Isd] Short-Time Protection Pick-Up Adjustment Range	6...14 x In

Environment

Standards	IEC 60947-2
Product Certifications	ASEFA KEMA LCIE ASTA
Pollution Degree	3 conforming to IEC 60947
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
------------------------------	---

Contractual warranty

Warranty	18 months
----------	-----------