



Main

Range of product	Masterpact NT
Range	Masterpact
Device short name	Gear motor MCH
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	MasterPact NT circuit breaker
[Uc] control circuit voltage	220...240 V AC 50/60 Hz

Complementary

Control type	Motor mechanism
Maximum charging time	3 s
Maximum power consumption in VA	180 VA
Accessory / separate part category	Spare parts for Masterpact NT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	820 g
Package 1 Height	6.4 cm
Package 1 width	12.8 cm
Package 1 Length	17.6 cm
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Weight	13.804 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

Contractual warranty

Warranty	18 months
----------	-----------