

Product datasheet

Specifications



Resistor adapter for gear motor,
fixed MasterPact NT, MCH
277/415VAC to MCH 440/480VAC,
spare part

33193

❗ Discontinued

Main

Range Of Product	MasterPact NT
Range	MasterPacT
Product Or Component Type	Resistor
Device Application	Automatic spring charging
Range Compatibility	Masterpact MasterPact NT circuit breaker
[Uc] Control Circuit Voltage	440...480 V AC 50/60 Hz

Complementary

Control Type	Motor mechanism
Maximum Charging Time	3 s
Maximum Power Consumption In Va	180 VA
Accessory / Separate Part Category	Spare parts for MasterPact NT

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.8 cm
Package 1 Length	9.0 cm
Package 1 Weight	132.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.755 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information