



Auxiliary contact 1 NC standard - for Fupact INF32 to 800

49610

! Discontinued on: 1 Dec 2021

! Discontinued

Main

Range Of Product	INF40 INF32 INF63 INF100160 INF200800
Range	FuPact
Device Short Name	auxiliary contact
Product Or Component Type	Auxiliary contact
Device Application	Connection
Range Compatibility	FuPact Fupact INF fuse-switch disconnector
Auxiliary Contacts Type	Standard
Signal Contacts Composition	1 NC
[Ith] Conventional Free Air Thermal Current	16 A

Complementary

Mounting Mode	Left hand side	
Output Contact Breaking	AC-15: 6 A at 24 V AC 50/60 Hz	
Capacity	AC-15: 6 A at 48 V AC 50/60 Hz	
	DC-12: 6 A at 24 V DC	
	AC-15: 2 A at 660/690 V AC 50/60 Hz	
	AC-15: 3 A at 440 V AC 50/60 Hz	
	AC-15: 4 A at 380/415 V AC 50/60 Hz	
	AC-15: 6 A at 110 V AC 50/60 Hz	
	AC-15: 6 A at 220/240 V AC 50/60 Hz	
	AC-15: 6 A at 250 V AC 50/60 Hz	
	DC-12: 0.1 A at 380/415 V DC	
	DC-12: 0.1 A at 440 V DC	
	DC-12: 0.4 A at 220/240 V DC	
	DC-12: 0.4 A at 250 V DC	
	DC-12: 1.1 A at 110 V DC	
	DC-12: 2 A at 48 V DC	
Minimum Load	10 mA at 24 V	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	10 cm
Package 1 Length	10 cm

Package 1 Weight

10 g

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

9	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile