



### Main

Range compatibility	Easergy T300 Easergy Flair
Product or component type	Indicator lamp
Device short name	BVE
Fixing mode	By 2 screws, with diameter 4 mm
[Us] rated supply voltage	3.6 V, <40 mA
Mounting mode	Wall mount

### Complementary

Connections - terminals	Screw terminals 3, cable cross section: 1.5 mm <sup>2</sup>
Local signalling	LED
Luminous flux	6 lm
Width	70 mm
Height	121 mm
Depth	150 mm
Net weight	0.147 kg

### Environment

IP degree of protection	IP54
IK degree of protection	IK09

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	150 g
Package 1 Height	7 cm
Package 1 width	8.7 cm
Package 1 Length	13 cm
Unit Type of Package 2	S04
Number of Units in Package 2	64

Package 2 Weight	10.2 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>