



ⓘ Discontinued

Commercial status

To be discontinued on: 30 June 2021

To be end-of-service on: 30 September 2021

Main

Range	Multi 9
Product name	Multi 9 GFP
Product or component type	Residual current circuit breaker (RCCB)
Device short name	GFP
Poles description	2P
Neutral position	Left
[In] rated current	25 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC-SIE
Rated conditional short-circuit current	10 kA
Utilisation category	AC-23A

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	230/240 V AC 50 Hz 120/240 V AC 60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	Fault indication
9 mm pitches	4
Height	81 mm
Width	36 mm
Depth	75 mm
Net weight	220 g
Colour	Grey

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical durability	20000 cycles
Provision for padlocking	Padlockable
Locking options description	Padlocking in OFF position
Connections - terminals	Tunnel type terminals 2.5...35 mm ² flexible Tunnel type terminals 2.5...35 mm ² rigid
Tightening torque	3.5 N.m

Environment

Standards	IEC 61008 UL 1053
IP degree of protection	IP20 conforming to IEC 60529 IP40 conforming to IEC 60529 IPxx B conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Package 1 Weight	0.221 kg
Package 1 Height	0.850 dm
Package 1 width	0.400 dm
Package 1 Length	0.900 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------