



# Category5e, 25pr UTP Cable 305m/reel Grey, CMR



ACT25P5EUCR3RGY

### Main

Range	Actassi
Product Or Component Type	Copper cable
Colour Tint	Grey
Cable Shielding Type	U/UTP

## Complementary

Type Of Cable	Multipair cable
Communication Network Category	5e
Maximum Loop Resistance	93.8 Ohm
Capacitance Unbalance	330 pF / 100 m
Maximum Resistance Unbalance	5 %
Wire Insulation Material	PE
Awg Gauge	AWG 24
Cable Outer Diameter	12.5 mm
Cable Length	305 m
Cable Weight	184 kg

#### **Environment**

Ambient Air Temperature For Operation	-2060 °C
Flame Retardance	CMR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.0 cm
Package 1 Width	40.0 cm
Package 1 Length	63.0 cm
Package 1 Weight	65.5 kg

## **Contractual warranty**

Warranty 18 months	
--------------------	--



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations