



1 Gang 1 Way Horizontal Dolly Switch w/ Green Fluorescent Indicator, Grey Silver

E3031H1_FGGS

! Discontinued on: 30 Jun 2023

(!) Discontinued

Main

Range	Neo	
Wiring Device Mounting	Surface Flush	
Switch Function	1-way	
Switch Application	Switch	
Load Type	Fluorescent lamp Resistive Incandescent lamp Inductive	
Bulb Type	Fluorescent (green)	
Colour Tint	Grev silver	

Complementary

Rated Current	10 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	EN 60669-1 GB 16915.1 IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	558 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations