

Product datasheet

Specifications



10A Mechanical Curtain Switch with Fluorescent Locator, White

E8231CF_WE

⚠ Discontinued on: 2 Apr 2021

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Curtain switch
Load Type	Resistive Fluorescent
Cover Frame Colour Tint	White

Complementary

Device Mounting	Flush Surface
Wiring Device Mounting	Flush Surface
Switch Function	Switch
Rated Current	10 A at 250 V AC 50 Hz
Local Signalling	Fluorescent (white)
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 1.5 mm ² for stranded cable(s) 1 x 2.5 mm ² for solid cable(s)
Embedding Depth	22.6 mm
Width	87 mm
Height	87 mm
Depth	22.6 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS EN 60669-1 MS IEC 60669-1 IEC 60669-1 GB 16915.1

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	98.58 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	591.48 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	32.5 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	5914.8 g

Contractual warranty

Warranty	18 months
----------	-----------