

Product datasheet

Specifications



Pieno - universal dimmer with switch - 1G - 450 W 250 V - white

E8232RD450U_WE_C5

Main

Range	Pieno
Product or component type	Dimmer
Power range	450 W LV halogen
[Ue] rated operational voltage	250 V AC 50 Hz
Number of gangs	1 gang
Cover frame colour tint	White

Complementary

Wiring device mounting	Flush Surface
Width	87 mm
Height	87 mm
Depth	47 mm
Connections - terminals	Pillar terminals

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60669

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	104.53 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9.5 cm

Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	637.18 g
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6271.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)