Product datasheet





Switch, AvatarOn, 1-pole 1-way, LED, brass terminal, IP20, wine gold

E8331L1LED_WG_C5

Main

Product Or Component Type	Switch
Device Application	Control
Load Type	Fluorescent lamp
	Inductive
	Resistive
	Incandescent lamp
Colour Tint	Wine gold

Complementary

Device Presentation	Complete product	
Rated Current	16 AX at 250 V AC 50/60 Hz	
Switch Function	1-pole 1-way	
Number Of Gangs	1 gang	
Number Of Rocker	1	
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s) 3 x 2.5 mm² for stranded cable(s) 4 x 1.5 mm² for solid cable(s) 4 x 1.5 mm² for stranded cable(s)	
Connections - Terminals	Brass terminal	
Local Signalling	Off: LED indicator, LED (amber)	
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator	
Device Mounting	Flush Surface	
Width	86 mm	
Height	86 mm	
Depth	34.2 mm	

Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	45 °C
Operating Altitude	2000 m
Relative Humidity	095 %
Environmental Characteristic	UV resistant

Life Is On Schneider 24 Apr 2024



Standards SS 227-1

MS IEC 60669-1 BS EN 60669-1 IEC 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	79.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	867.0 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations