

Product datasheet

Specifications



GALAXY VM System Bypass Cabinet 640KVA 380/400/415V EL

GVMSBC640KHEL

Overview

Presentation	System bypass cabinet for use in a parallel configuration with up to a 640kVA maximum load capacity.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	400 V 3 phases

Physical

Height	197 cm
Width	71.2 cm
Depth	85.9 cm
Net Weight	328 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	50/60 Hz
-------------------	----------

Conformance

Product Certifications	C-Tick CE RCM
Standards	EN/IEC 62040-1 EN/IEC 62040-2 EN/IEC 62040-3 IBC 2012 and CBC2013 to Sds=2.02g UL 1778 VFI-SS-111

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-25...65 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage Relative Humidity	0...95 %
Storage Altitude	0.00...14999.82 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	198 cm
Package 1 Width	88.9 cm
Package 1 Length	71.5 cm
Package 1 Weight	350 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)