



Main

Product or component type	Cover frame
Device short name	KB30

Complementary

Number of gangs	1 gang
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround
Projecting depth	8 mm
Device mounting	Flush
Width	86 mm
Height	86 mm

Environment

Standards	BS 5733
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

Packing Units

Package 1 Weight	42.500 g
Package 1 Height	1.000 mm
Package 1 width	1.000 mm
Package 1 Length	1.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------