



# DISTRIBUTION LENGTH 20A 24M

KDP20ED424120

! Discontinued

#### Main

Range Of Product	Canalis	
Product Or Component Type	Busbar trunking	
Product Compatibility	KDP	
Busbar Description	Flexible bar	

### Complementary

Device Application	Lighting Power socket distribution	
[Ue] Rated Operational Voltage	230400 V	
[Uimp] Rated Impulse Withstand Voltage	4 kV	
[Ui] Rated Insulation Voltage	690 V	
[le] Rated Operational Current	20 A at 35 °C	
[Icw] Rated Short-Time Withstand Current	0.34 kA	
[lpk] Rated Peak Withstand Current	3.6 kA	
Network Frequency	50/60 Hz	
Maximum Radiated Magnetic Field	2 pT	
Thdi	015 % 20 A 1533 % 16 A 33100 % 14 A	
Maximum Voltage Drop	<0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.65 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.58 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.5 V with power factor = 0.7 at 50 Hz with 1A for 100 m long	
Busbar Trunking Polarity	L2 + L1 + L3 + N + PE	
Tap-Off Unit Interval	1200 mm	
Type Of Packing	Spool	
Standards	EN/IEC 60439-2 EN/IEC 61439-6	
Length	23 m	
Net Weight	7.68 kg	

#### **Environment**

Ip Degree Of Protection IP55 conforming to IEC 60529

Ik Degree Of Protection	IK07 conforming to IEC 62262	
Ambient Air Temperature For Operation	3540 °C (93 % of In) 4045 °C (85 % of In) 4550 °C (76 % of In) 5055 °C (66 % of In) 035 °C (100 % of In)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)