

# Product datasheet

Specifications



## EVlink Residential - wall-mounted - 3.7 kW - socket-outlet T3 - charging station

NCA19130

⚠ Discontinued on: 15 Dec 2015

⚠ Discontinued

### Main

Range	EVlink
Product Name	EVlink residential
Product Or Component Type	Charging station
Poles Description	1P + N
Mounting Mode	Wall-mounted
Offer Type	Standard
Nominal Output Power	3.7 kW
Number Of Charge Point	1
Number Of Charge Point	Socket-outlet T3

### Complementary

[Us] Rated Supply Voltage	230 V AC 50/60 Hz
Earthing System	TN TT
Control Type	1 white button, function: stop 1 white button, function: start
Local Signalling	8 green LED, function: on charge 1 green LED, function: socket connected 1 red LED, function: fault 1 green LED, function: power ON 1 LED, function: stop
Height	323 mm
Width	242 mm
Depth	100 mm
Net Weight	2.5 kg
Standards	IEC 61851-22 IEC 61851-1
Product Certifications	CB CE

### Environment

Ip Degree Of Protection	IP41 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...50 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-50...80 °C
Operating Altitude	0...2000 m
Relative Humidity	0...93 %

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14 cm
Package 1 Width	37 cm
Package 1 Length	40 cm
Package 1 Weight	3.209 kg