# **Product datasheet**

Specifications





# Spacial SF enclosure with mounting plate - assembled - 2000x1000x500 mm

NSYSF201050P

### Main

Range	Spacial	
Extended Range	Spacial SF	
Application	Multi-purpose	
Product Or Component Type	Suitable enclosure	
Enclosure Nominal Height	2000 mm	
Enclosure Nominal Width	1000 mm	
Enclosure Nominal Depth	500 mm	
Enclosure Mounting	Floor-standing	
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 1 mounting plate	

## Complementary

Structure Type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm	
Door Opening Side	Reversible (120 °)	
Door Type	Plain front	
Mounting Plate Description	Plain	
Type Of Gland Plate	Without gland plate	
Lock Type	4 points lock, handle with 5 mm double bar insert front door	
Number Of Doors	Front: 1 door(s)	
Accessibility For Operation	Sides of enclosure Rear Front	
Removable Parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws	

Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net Weight	162.023 kg

## **Environment**

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.0 cm
Package 1 Width	104.0 cm
Package 1 Length	58.0 cm
Package 1 Weight	161.078 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations