# **Product datasheet**

Specifications





# Pragma surface enclosure - IP30 - 1 x 13 modules - transparent door

PRA29113

- ! Discontinued on: 30 Jun 2023
- ! End-of-service on: 31 Oct 2023

① Discontinued

#### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	336 mm outside:
Height	300 mm
Depth	143 mm
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

## Complementary

Enclosure Mounting	Surface
9 Mm Pitches	26
Total Number Of 18 Mm Modules	13
Power Dissipation In W	22 W
[In] Rated Current	63 A
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Cable Entry	Trunking
	Cut-out plates
	Cable or tube
	Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 14 outgoers
	1 neutral (Quick) with 14 outgoers
Distribution Block Outgoers	3 x 25 mm² for earth
-	11 x 4 mm <sup>2</sup> for earth
	3 x 25 mm² for neutral
	11 x 4 mm² for neutral
Enclosure Material	Back part: technoplastic
	Front face: technoplastic

Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: colourless
Market Segment	Small commercial Residential
Embedding Depth	95 mm
Internal Depth	95 mm

## **Environment**

Fire Resistance	Back part: 650 °C Front face: 650 °C Door: 650 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-2560 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	42.0 cm
Package 1 Length	38.0 cm
Package 1 Weight	2.68 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations