

# Product datasheet

Specifications



## Ulti - 250V 16 AX 1 gang 2-way impress switch module, blue LED

U201SPM-2\_B00

### Main

Range	Ulti
Product Or Component Type	Switch module
Load Type	Fluorescent
Switch Application	Switch

### Complementary

Bulb Type	LED blue
Rated Current	16 AX at 250 V AC 50 Hz
Number Of Cables	3 cable(s) 2.5 mm²
Opening Distance	> 3 mm
Device Mounting	Flush
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Number Of Gangs	1 gang
Switch Function	2-way
Width	87 mm
Height	87 mm
Depth	23.3 mm

### Environment

Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	0...95 %
Standards	BS EN 60669-1
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications