



Glavno

Range	Prisma
Range compatibility	Prisma G Prisma Pack 250
Product or component type	Rail
Accessory / separate part category	Installation accessory
Type of rail	Modular
Installed device	Multi 9: fixed modular device Acti 9: fixed modular device Vigirex: RH10 Vigirex: RH21 Vigirex: RH99 TeSys: fixed GV2LE TeSys: fixed GV2ME TeSys: fixed GV2RTn Multi 9: fixed modular device <= 40 A Acti 9: fixed modular device <= 40 A Multi 9: fixed NG125 with earth leakage protection - control: toggle Multi 9: fixed NG125 without earth leakage protection - control: toggle Multi 9: fixed NG125 NA - control: toggle Acti 9: fixed C120 with earth leakage protection - control: toggle Acti 9: fixed C120 without earth leakage protection - control: toggle Vigilohm: fixed IM9 Vigilohm: fixed IM9-OL Vigilohm: IM20 Vigilohm: IM20H Compact: fixed INS40 - control: direct front rotary handle - vertical installation Compact: fixed INS63 - control: direct front rotary handle - vertical installation Compact: fixed INS100 - control: direct front rotary handle - vertical installation Compact: fixed INS125 - control: direct front rotary handle - vertical installation Compact: fixed INS160 - control: direct front rotary handle - vertical installation Acti 9: fixed iC120 with earth leakage protection - control: toggle Acti 9: fixed iC120 without earth leakage protection - control: toggle Acti 9: fixed 1/2 or 1 module lamp - horizontal installation Acti 9: fixed measurement device - horizontal installation Multi 9: fixed measurement device - horizontal installation
Poles description	9 x 3P: fixed: GV2LE 9 x 3P: fixed: GV2ME 9 x 3P: fixed: GV2RTn 1 x 3P: fixed: NG125

Izjava: Ovi dokumenti ne mijenjaju niti su namijenjeni utvrđivanju primjerenosti ili pouzdanosti ovih proizvoda u specifičnim korisničkim primjenama.

1 x 3P: fixed: NG125 NA
 1 x 3P: fixed: C120
 1 x 4P: fixed: NG125
 1 x 4P: fixed: NG125 NA
 1 x 4P: fixed: C120
 1 x 3P: fixed: INS40 vertical installation
 1 x 3P: fixed: INS63 vertical installation
 1 x 3P: fixed: INS100 vertical installation
 1 x 3P: fixed: INS125 vertical installation
 1 x 3P: fixed: INS160 vertical installation
 1 x 3P: fixed: iC120
 1 x 4P: fixed: INS40 vertical installation
 1 x 4P: fixed: INS63 vertical installation
 1 x 4P: fixed: INS100 vertical installation
 1 x 4P: fixed: INS125 vertical installation
 1 x 4P: fixed: INS160 vertical installation
 1 x 4P: fixed: iC120

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Pack enclosure - width 600 mm
Number of vertical modules [50 mm]	2 module(s) : 1/2 or 1 module lamp , direct in 600 mm Wide floor-standing enclosure 2 module(s) : 1/2 or 1 module lamp , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : C120 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 5 module(s) : C120 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2LE , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2LE , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2ME , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2ME , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2RTn , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2RTn , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : iC120 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 5 module(s) : iC120 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : IM20 in 600 mm Wide floor-standing enclosure 3 module(s) : IM20 in 600 mm Wide wall-mounted enclosure 3 module(s) : IM20H in 600 mm Wide floor-standing enclosure 3 module(s) : IM20H in 600 mm Wide wall-mounted enclosure 3 module(s) : IM9 in 600 mm Wide floor-standing enclosure 3 module(s) : IM9 in 600 mm Wide wall-mounted enclosure 3 module(s) : IM9-OL in 600 mm Wide floor-standing enclosure 3 module(s) : IM9-OL in 600 mm Wide wall-mounted enclosure 4 module(s) : INS100 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS100 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : INS100 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : INS100 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS125 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS125 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : INS125 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : INS125 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS160 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS160 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : INS160 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : INS160 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS40 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS40 , direct in 600 mm Wide wall-mounted enclosure 4 module(s) : INS63 , direct in 600 mm Wide floor-standing enclosure 4 module(s) : INS63 , direct in 600 mm Wide wall-mounted enclosure 2 module(s) : measurement device , direct in 600 mm Wide floor-standing enclosure 2 module(s) : measurement device , direct in 600 mm Wide wall-mounted enclosure 2 module(s) : measurement device , direct in 600 mm Wide Pack enclosure 3 module(s) : modular device <= 40 A , direct in 600 mm Wide floor-standing enclosure 3 module(s) : modular device <= 40 A , direct in 600 mm Wide wall-mounted enclosure 8 module(s) : modular device <= 40 A , direct in 600 mm Wide floor-standing enclosure 8 module(s) : modular device <= 40 A , direct in 600 mm Wide wall-mounted enclosure 6 module(s) : modular device <= 40 A , direct in 600 mm Wide Pack enclosure 6 module(s) : modular device , direct in 600 mm Wide Pack enclosure 4 module(s) : modular device , direct in 600 mm Wide floor-standing enclosure 4 module(s) : modular device , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : NG125 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 5 module(s) : NG125 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure

5 module(s) : NG125 NA , direct in 600 mm Wide floor-standing enclosure
 5 module(s) : NG125 NA , direct in 600 mm Wide wall-mounted enclosure
 3 module(s) : RH10 , direct in 600 mm Wide floor-standing enclosure
 3 module(s) : RH10 , direct in 600 mm Wide wall-mounted enclosure
 3 module(s) : RH21 , direct in 600 mm Wide floor-standing enclosure
 3 module(s) : RH21 , direct in 600 mm Wide wall-mounted enclosure
 3 module(s) : RH99 , direct in 600 mm Wide floor-standing enclosure
 3 module(s) : RH99 , direct in 600 mm Wide wall-mounted enclosure
 5 module(s) : C120 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 5 module(s) : C120 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure
 5 module(s) : iC120 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 5 module(s) : iC120 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure
 5 module(s) : NG125 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 5 module(s) : NG125 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure

9 mm pitches	48
Quantity per set	Set of 1
Height	93.5 mm
Width	600 mm
Depth	50 mm
Product weight	0.24 kg
Colour	Grey

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Ekološki profil proizvoda
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------