



Main

Range	Prisma
Product name	Prisma P
IP degree of protection	IP30
Product or component type	Door
Enclosure mounting	Floor-standing
Type of door	Plain
Provided equipment	Door Handle Keylock (key 405) Hinge Other keylock and insert (to be ordered separately)

Complementary

Door opening side	Reversible
Number of locks	3
Door opening angle	120 °
Installation description	Cubicle - width 650 + 150 mm Cubicle - width 800 mm
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	2000 mm
Width	800 mm
Product weight	30.34 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
-------------------------	---------------------------------

Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1018 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available