Product datasheet

Specifications

, → Green Premium[™]



FRONT PLATE CVS250 HORIZONTAL FIXED TOGGLE W850 4M

03256

Discontinued on: May 12, 2023

(!) Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Type Of Front Plate	Cut-out
Installed Device	EasyPact: fixed CVS100160 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: mounting plate support: CVS100160 horizontal installation 1 x 4P: mounting plate support: CVS100160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation
Operating Position	Horizontal

Complementary

· · · · · · · · · · · · · · · · · · ·	
Enclosure/Cubicle Description	Floor-standing enclosure - width 850 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	850 mm
Net Weight	1.42 kg
Quantity Per Set	Set of 1

850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed toggle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed toggle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed toggle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed toggle horizontal 4P 1 direct with long terminal shield 4

Environment

Ip Degree Of Protection

IP30

Packing Units

r doking onits	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	20.0 cm
Package 1 Length	75.0 cm
Package 1 Weight	1.42 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	19.0 cm
Package 2 Width	23.0 cm
Package 2 Length	76.0 cm
Package 2 Weight	14.76 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	60
Package 3 Height	34.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	97.2 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile