

Product datasheet

Specifications



modular bell - 230 V 50/60Hz - 80 dB

15320

⚠ Discontinued on: Jun 13, 2023

⚠ Discontinued

Main

Range Of Product	Domae
Product Or Component Type	Bell
Device Short Name	SO

Complementary

[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Power Consumption In Va	5 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	72 mm
Net Weight	77 g
Auxiliary Connection Terminal	Tunnel type terminalsrigid 4 mm ² Tunnel type terminalsflexible 4 mm ² Tunnel type terminalsflexible with ferrule 4 mm ²
Wire Stripping Length	12 mm for bottom connection
Tightening Torque	1.3 N.m bottom

Environment

Noise Level	80 dB
Type Of Sound	Bell
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient Air Temperature For Operation	-10...40 °C
Ambient Air Temperature For Storage	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	6.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	59 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8 cm
Package 2 Width	10 cm
Package 2 Length	22.5 cm
Package 2 Weight	758 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.548 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins