



Gear motor MCH, drawout MasterPact NW, 100/130VAC 50/60Hz

48526

Main

Device Short Name	gear motor MCH
Product Or Component Type	Gear motor mechanism MCH
Device Application	Automatic spring charging
Range Compatibility	Masterpact MasterPact NW circuit breaker
Control Type	Motor mechanism
[Uc] Control Circuit Voltage	100130 V AC 50/60 Hz
Circuit Breaker Mounting Mode	Drawout

Complementary

Maximum Charging Time	4 s
Maximum Power Consumption In Va	180 VA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.6 cm
Package 1 Width	12.9 cm
Package 1 Length	22.9 cm
Package 1 Weight	1.86 kg

Contractual warranty

Warranty	18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information