Product datasheet





Circuit breaker frame, MasterPact NW08H10, 800A, 50kA/1150VAC 50/60Hz (Icu), 3 poles, drawout, without control unit

48725

Main

Range	MasterPacT	
Product Name	MasterPact NW	
Circuit Breaker Name	MasterPact NW08H10	
Product Or Component Type	Circuit breaker	
Device Application	Power distribution protection	
Poles Description	3P	
Control Unit	Without control unit	
[In] Rated Current	800 A at 40 °C	
Performance Type	H10 50 kA 1150 V AC	
[Ue] Rated Operational Voltage	1150 V AC 50/60 Hz	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Selectivity Category	Category B	
Control Type	Push-button	
Mounting Mode	Drawout	

Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	50 kA at 1150 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	50 kA at 1150 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	50 kA 1 s 50 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	105 kA 1150 V AC at 50/60 Hz
Sensor Rating	400 A 800 A
[Ui] Rated Insulation Voltage	1250 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Mounting Support	Backplate Rails
Upside Connection	Rear
Downside Connection	Rear
Connection Pitch	115 mm

Life Is On Schneider Apr 25, 2024

Mechanical Durability	12500 cycles without maintenance 25000 cycles with maintenance
Electrical Durability	500 cycles 1150 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2
Height	439 mm
Width	441 mm
Depth	395 mm
Net Weight	90 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2
Product Certifications	CE CCC EAC

Environment

Ip Degree Of Protection	IP30 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	02000 m without derating 2000 m5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	0.1 cm
Package 1 Length	0.2 cm
Package 1 Weight	47.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information