# **Product datasheet**

Specifications





1A/5A CT + IO current connector CCA634 for Sepam series 20, 40, 60, 80

59629

### Main

| Accessory / Separate Part Type | CT + IO current connector |
|--------------------------------|---------------------------|
| Range Of Product               | Sepam series 40           |
|                                | Sepam series 80           |
|                                | Sepam series 20           |
|                                | Sepam series 60           |
|                                | Sepam series 80 NPP       |
| Device Short Name              | CCA634                    |

### Complementary

Auxiliary Connection Terminal Ring lugs 4 mm 1.5...6 mm<sup>2</sup>

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 6.0 cm   |
| Package 1 Width              | 12.5 cm  |
| Package 1 Length             | 18.3 cm  |
| Package 1 Weight             | 410.0 g  |
| Unit Type Of Package 2       | S03      |
| Number Of Units In Package 2 | 16       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 7.033 kg |

### **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>②</b> | Toxic Heavy Metal Free     |     |
| <b>9</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |