

Product datasheet

Specifications



Acti9 iLL Three-phase voltage indicator light - Red - 230-400 Vac

A9E18327

! Discontinued on: Nov 1, 2020

! Discontinued

Main

Range Of Product	Acti9
Product Name	Acti9 iLL
Product Or Component Type	Modular pilot lighth
Device Short Name	iLL
[Us] Rated Supply Voltage	230...400 V AC at 50/60 Hz

Complementary

Indicator Light	3 LEDs red, service life 100000 h of constant lighting efficiency (consumption 0.9 W)
Mounting Mode	Fixed
Mounting Support	Symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary Connection Terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm² Tunnel type terminal 2 cable(s) rigid 2.5 mm² Tunnel type terminal 1 cable(s) flexible 0.5 mm² Tunnel type terminal 2 cable(s) flexible 2.5 mm² Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm²
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	IEC 73 IEC 1000-4
Ip Degree Of Protection	IP2 IPxx B
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-35...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-40...80 °C
-------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	6.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	49.300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	10.000 cm
Package 2 Length	23.500 cm
Package 2 Weight	628.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.040 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.




[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free	
 RoHS Exemption Information	Yes
 Halogen Free Plastic Parts & Cables Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations