# **Product datasheet**





## modular single phase power meter iEM2000T - 230V - 40A without display

A9MEM2000T

Discontinued on: Nov 1, 2020



#### Main

Range	Acti9
Family	Acti9 iEM2000
Device Short Name	iEM2000T
Product Or Component Type	Energy meter

## Complementary

Poles Description	1P + N	
Type Of Measurement	Active power	
Device Application	Sub billing	
Accuracy Class	Class 1 active energy conforming to IEC 62053-21	
Input Type	Direct input	
Maximum Current [Imax]	40 A	
[lb] Basic Current	5 A	
Rated Current	40 A	
Rated Voltage	230 V +/- 20 %	
Network Frequency	60 Hz 50 Hz	
Frequency Measurement Range	4862 Hz	
Technology Type	Electronic	
Display Type	Without display	
Sampling Rate	32 samples/cycle	
Measurement Current	0.2540 A	
Display Digits	0	
Communication Port Protocol	-	
Communication Port Support	-	
Local Signalling	Green indicator light: power ON Yellow indicator light: metering and activity 3200 p/kWh	
Digital Inputs	0	
Digital Outputs	1 pulse energy monitoring:	
Output Voltage	535 V DC@20 mA	
Impulse Duration	120 ms	

Life Is On Schneider Apr 25, 2024

Maximum Power Consumption In Va	10 VA at 240 V AC
Mounting Mode	Clip-on
Mounting Support	DIN rail
Connections - Terminals	Power circuit: tunnel type terminals (bottom) 1 10 mm² cable(s) Remote transfer: tunnel type terminals (top) 1 4 mm² cable(s)
Tightening Torque	Power circuit: 1.2 N.m Remote transfer: 0.8 N.m
Standards	IEC 61557-12 IEC 62053-21
Product Certifications	CE

## **Environment**

Ip Degree Of Protection	IP40 front panel: conforming to IEC 60529 IP20 casing:
Ambient Air Temperature For Operation	-2565 °C -2055 °C
Ambient Air Temperature For Storage	-4070 °C
Operating Altitude	< 2000 m
Relative Humidity	095 % at 55 °C
Colour	White
9 Mm Pitches	2
Width	18 mm
Height	96.5 mm
Depth	69 mm
Net Weight	0.073 kg

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	112.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	38
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.982 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information