



Category5e, 4pr FTP Cable 305m Blue, CM



ACT4P5ESCM3RBBU

! Discontinued on: Jun 30, 2023

① Discontinued

Main

Range	Actassi
Product Or Component Type	Copper cable
Colour Tint	Blue
Cable Shielding Type	F/UTP

Complementary

Type Of Cable	4 pair cables
Communication Network Category	5e
Minimum Return Loss	Guaranteed: 20 dB at 1 MHz
	Guaranteed: 23 dB at 4 MHz
	Guaranteed: 25 dB at 10 MHz
	Guaranteed: 25 dB at 16 MHz
	Guaranteed: 25 dB at 20 MHz
	Guaranteed: 24.3 dB at 25 MHz
	Guaranteed: 23.6 dB at 31.25 MHz
	Guaranteed: 21.5 dB at 62.5 MHz
	Guaranteed: 20.1 dB at 100 MHz
	Guaranteed: 25 dB at 8 MHz
Attenuation	Guaranteed: 2 dB @ 1 MHz per 100 m cable
	Guaranteed: 4.1 dB @ 4 MHz per 100 m cable
	Guaranteed: 5.8 dB @ 8 MHz per 100 m cable
	Guaranteed: 6.5 dB @ 10 MHz per 100 m cable
	Guaranteed: 8.2 dB @ 16 MHz per 100 m cable
	Guaranteed: 9.3 dB @ 20 MHz per 100 m cable
	Guaranteed: 10.4 dB @ 25 MHz per 100 m cable
	Guaranteed: 11.7 dB @ 31.25 MHz per 100 m cable
	Guaranteed: 17 dB @ 62.5 MHz per 100 m cable
	Guaranteed: 22 dB @ 100 MHz per 100 m cable
Power Sum Near-End Crosstalk	Guaranteed: 62.3 dB at 1 MHz
[Psnext]	Guaranteed: 53.3 dB at 4 MHz
	Guaranteed: 48.8 dB at 8 MHz
	Guaranteed: 47.3 dB at 10 MHz
	Guaranteed: 42.8 dB at 20 MHz
	Guaranteed: 41.3 dB at 25 MHz
	Guaranteed: 39.9 dB at 31.25 MHz
	Guaranteed: 35.4 dB at 62.5 MHz
	Guaranteed: 32.3 dB at 100 MHz
	Guaranteed: 44.2 dB at 16 MHz
Near End Crosstalk [Next]	Guaranteed: 65.3 dB at 1 MHz
	Guaranteed: 56.3 dB at 4 MHz
	Guaranteed: 51.8 dB at 8 MHz
	Guaranteed: 50.3 dB at 10 MHz
	Guaranteed: 47.3 dB at 16 MHz
	Guaranteed: 45.8 dB at 20 MHz
	Guaranteed: 44.3 dB at 25 MHz
	Guaranteed: 42.9 dB at 31.25 MHz
	Overgrands and OO A dip at CO 5 Miles

Guaranteed: 38.4 dB at 62.5 MHz Guaranteed: 35.3 dB at 100 MHz

Maximum Loop Resistance	93.8 Ohm
Capacitance Unbalance	330 pF / 100 m
Wire Insulation Material	PE
Awg Gauge	AWG 24
Cable Outer Diameter	5 mm
Cable Length	305 m
Cable Weight	42 kg

Environment

Ambient Air Temperature For Operation	-2060 °C
Flame Retardance	CM

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17 cm
Package 1 Width	15 cm
Package 1 Length	35 cm
Package 1 Weight	12500 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations